




# ENAPART



93 S Railroad Avenue Unit C  
Bergenfield NJ 07621 USA  
[www.enapart.com](http://www.enapart.com)  
[sales@enapart.com](mailto:sales@enapart.com)



Via del Canneto 35,  
Borgosatollo, Brescia - Italia  
[www.enapart.it](http://www.enapart.it)  
[vendite@enapart.it](mailto:vendite@enapart.it)



Barbaros Mah. Ihlamur Bul. Ağaoğlu  
My Newwork No:3/15 Ataşehir / İstanbul  
[www.enapart.net](http://www.enapart.net)  
[satis@enapart.net](mailto:satis@enapart.net)



PRIVADA 10 B SUR #3908 COL.  
ANZUREZ, C.P. 72530, PUEBLA, PUE  
[www.enapart.com.mx](http://www.enapart.com.mx)  
[sales@enapart.com.mx](mailto:sales@enapart.com.mx)



Friedrich-Ebert-Anlage 36, 60325  
Frankfurt am Main, Germany  
[www.enapart.de](http://www.enapart.de)  
[anfrage@enapart.de](mailto:anfrage@enapart.de)



4 boulevard Carnot, 95400  
villiers-le-bel, Paris, France  
[www.enapart.fr](http://www.enapart.fr)  
[sales@enapart.fr](mailto:sales@enapart.fr)



65049, ОДЕСА, ВУЛИЦЯ ІВАНА  
ФРАНКА, БУДИНОК 55, ПОВЕРХ 3  
[www.enapart.com.ua](http://www.enapart.com.ua)  
[sales@enapart.com.ua](mailto:sales@enapart.com.ua)



MUNICIPIUL BUCUREȘTI, SECTOR 3,  
B-DUL BASARABIA, NR.250, CORP P+5  
[www.enapart.ro](http://www.enapart.ro)  
[sales@enapart.ro](mailto:sales@enapart.ro)



〒584-0023 大阪府富田林市若松町  
東2丁目2番16号  
[www.enapart.co.jp](http://www.enapart.co.jp)  
[sales@enapart.co.jp](mailto:sales@enapart.co.jp)



PLAZA NUESTRA SEÑORA DE LAS  
NIEVES 12 ,LOCAL ,50012,ZARAGOZA  
[www.enapart.es](http://www.enapart.es)  
[ventas@enapart.es](mailto:ventas@enapart.es)



Складова база „Онгъл“, Склад А2, п.к.  
4006, гр. Пловдив, България  
[www.enapart.bg](http://www.enapart.bg)  
[sales@enapart.bg](mailto:sales@enapart.bg)



3 Austin Mews, High Street, Hemel  
Hempstead, HP1 3AF , United Kingdom  
[www.enapart.co.uk](http://www.enapart.co.uk)  
[sales@enapart.co.uk](mailto:sales@enapart.co.uk)

## Vapac

Enapart always strives to provide the competitive prices and timings of supplies for its customers. We sell only original equipment and spare parts, although we are not always the official distributor or manufacturer's dealer. All displayed trademarks and part numbers are the property of their respective owners.

### BRAND'S PRODUCTS

| Product                                                | Description                                  |
|--------------------------------------------------------|----------------------------------------------|
| <a href="#">2160120</a>                                | Gasket filling and drain base                |
| <a href="#">8402 (630-LE)</a>                          | Hauptplatine LE                              |
| <a href="#">1150634 für LE 45 D</a>                    | Konfigurationskarte LE/LEP                   |
| <a href="#">M570003</a>                                | electrode cap black                          |
| <a href="#">LE18LC</a>                                 | Steam Humidifiers                            |
| <a href="#">LE60D</a>                                  | Dampfluftbefeuchter                          |
| <a href="#">PCD4N-6WB</a>                              | Spare cylinder 4N-6WB                        |
| <a href="#">61-PCD4H-6WB</a>                           | Cylinder                                     |
| <a href="#">Steam Cylinder for VAPAC( S/N V36896 )</a> | Steam Cylinder                               |
| <a href="#">CC1/2N-2WA (C1-2N235)</a>                  | partb. replacement cylinder                  |
| <a href="#">PCD1/2N-2W</a>                             | cylinder                                     |
| <a href="#">CC-4H-6WB , LE110D</a>                     |                                              |
| <a href="#">CC-4H-6WB , LE90D</a>                      |                                              |
| <a href="#">CC-4H-3WB , LE30D</a>                      |                                              |
| <a href="#">1240122</a>                                | Transformer                                  |
| <a href="#">PCD4L-3WB</a>                              |                                              |
| <a href="#">LE05D</a>                                  | Electrode Boiler                             |
| <a href="#">633</a>                                    |                                              |
| <a href="#">LR10C</a>                                  | Cylinder                                     |
| <a href="#">PCD4N-3WB (150-650 uS/cm)</a>              | Replacement cylinder                         |
| <a href="#">PCM2N-2WA</a>                              | Cylinder                                     |
| <a href="#">PCD4N-3WB (450-1000 uS/cm)</a>             |                                              |
| <a href="#">M520250</a>                                | Flexible hose connection for water inlet 3/4 |
| <a href="#">631-LE-M1</a>                              | PCB display LE humidifier + antistatic kit   |
| <a href="#">PCD4N-3WB Steam cylinder 4N-3WB</a>        | Steam cylinder                               |
| <a href="#">PCM3NS-3WA</a>                             | Cylinder                                     |
| <a href="#">PCD4NS-3WB</a>                             | Cylinder                                     |
| <a href="#">PCD4NS-6WB</a>                             | Cylinder                                     |
| <a href="#">PCM3N-3WA</a>                              | Cylinder                                     |
| <a href="#">LED18D</a>                                 | Steam Humidifiers                            |
| <a href="#">PCM2N-2W0</a>                              | moisture tank                                |
| <a href="#">FVKIT-108-1</a>                            | Humidity sensor for duct installation        |
| <a href="#">LE110D + LE90 (AHU B15-1)</a>              | Humidifier                                   |
| <a href="#">Typ LE110D + LE110 + LE30D (AHU B15-2)</a> | Humidifier                                   |
| <a href="#">LE110D + LE90 (AHU B15-3)</a>              | Humidifier                                   |
| <a href="#">LE110D + LE90 (AHU B15-4)</a>              | Humidifier                                   |

| Product                                               | Description                 |
|-------------------------------------------------------|-----------------------------|
| <a href="#">LE30D</a>                                 | steam humidifier            |
| <a href="#">PCD4H-6WB</a>                             | Cylinder                    |
| <a href="#">CC4H-6WB</a>                              | Cleanable Steam Cylinder    |
| <a href="#">2H-2WA</a>                                | Spare cylinder              |
| <a href="#">PCD1/2N-2WA</a>                           | Humidification cylinder     |
| <a href="#">PCM2N-2WA old code D2N235 new code</a>    | Humidification cylinder     |
| <a href="#">PCD4H-3WB</a>                             | cylinder                    |
| <a href="#">P/N: D2N235, Type: 2N-2WA</a>             | Replacement cylinders       |
| <a href="#">D4N355 4N-3WB</a>                         | Spare cylinder 4N 3WB       |
| <a href="#">Typ LE09LC</a>                            | steam humidifier            |
| <a href="#">LE30LC</a>                                | humidifier                  |
| <a href="#">Typ LR60PD</a>                            | Dampfluftbefeuchter         |
| <a href="#">8040721</a>                               | electrode cable             |
| <a href="#">656-LC</a>                                | LELC Mainboard              |
| <a href="#">1150633</a>                               | CART                        |
| <a href="#">FV-KIT 175</a>                            | Status / Failure Kit        |
| <a href="#">P/N: 105526, Type: TK1-528AB024MC2268</a> | SICHERHEITSSCHALTER         |
| <a href="#">630-LE</a>                                | motherboard for humidifier  |
| <a href="#">2600070</a>                               | Sludge pump                 |
| <a href="#">Typ LE18D</a>                             | Steam humidifier            |
| <a href="#">D4H655</a>                                | Cylinder                    |
| <a href="#">CC4N-6WB</a>                              |                             |
| <a href="#">D3N335</a>                                | 3N-3WA replacement cylinder |
| <a href="#">D4H355</a>                                | replacement cylinder        |
| <a href="#">D2H235</a>                                | Replacement Cylinder        |
| <a href="#">C4NS355</a>                               | Replacement Cylinder        |
| <a href="#">D1-2H235</a>                              | Spare Cylinder              |
| <a href="#">D2N235</a>                                | Spare Cylinder              |
| <a href="#">C4N655</a>                                | Spare Cylinder              |
| <a href="#">D4N655 (4N-6WB)</a>                       | Spare Cylinder              |
| <a href="#">1150575</a>                               | Operation board             |
| <a href="#">LE18LC-2</a>                              | steam humidifier            |
| <a href="#">D1-2HS335</a>                             | Spare Cylinder              |
| <a href="#">LE05LC-2</a>                              | steam humidifier            |
| <a href="#">D4H355 (4H-3WB)</a>                       | Spare Cylinder              |
| <a href="#">LMV2</a>                                  |                             |
| <a href="#">3N-3WA</a>                                | Replacement cylinder        |
| <a href="#">2620325</a>                               | Inlet valve                 |
| <a href="#">PCM1N-2WA old code/ new code D1N235</a>   | Spare Cylinder              |
| <a href="#">D1-2L222</a>                              | replacement cylinder        |
| <a href="#">RDU18LE</a>                               | Fan Attachment RDU          |
| <a href="#">C4H655</a>                                | .                           |
| <a href="#">40111318 Typ LE18LC</a>                   | Steam humidifier            |
| <a href="#">40111330 Typ LE30LC</a>                   | Steam humidifier            |
| <a href="#">D1-2L222 1/2L-2WO</a>                     |                             |

| Product                                                | Description                                         |
|--------------------------------------------------------|-----------------------------------------------------|
| <a href="#">LE90D</a>                                  | Humidifiers LE90D 90 kg/h — with Display            |
| <a href="#">3910021</a>                                | Drain sieve for LR cylinder                         |
| <a href="#">D4L355</a>                                 | Power with clock                                    |
| <a href="#">Typ CM2N-2WA old code/ new code 2N-2WA</a> | cylinder for steam humidifier LE09LC-2              |
| <a href="#">PCM1-3WO</a>                               | Replacement cylinders                               |
| <a href="#">D1N322</a>                                 | Replacement cylinders                               |
| <a href="#">D4N355</a>                                 | Replacement cylinder                                |
| <a href="#">Typ LE09D</a>                              | steam humidifier                                    |
| <a href="#">Typ LE90PD</a>                             | steam humidifier                                    |
| <a href="#">Typ LE45LC</a>                             | steam humidifier                                    |
| <a href="#">D1-2N235</a>                               | Replacement cylinder 1/2N-2WA                       |
| <a href="#">D1-2H235 1</a>                             | Replacement cylinder 1/2H-2WA                       |
| <a href="#">M990168</a>                                | Filling cup with stainless steel tubes              |
| <a href="#">3910110</a>                                | Housing base for limescale collector film           |
| <a href="#">2620351</a>                                | inlet valve                                         |
| <a href="#">LE30PD</a>                                 | steam humidifier                                    |
| <a href="#">2560047</a>                                | drain hose                                          |
| <a href="#">P/N: C4H355, Type: 4H-3WB</a>              | Replacement cylinders                               |
| <a href="#">P/N: C3N335, Type: 3N-3WA</a>              | Replacement cylinders                               |
| <a href="#">D3H335</a>                                 | Replacement cylinder                                |
| <a href="#">P/N: D4H355, Type: 4H-3WB</a>              | Replacement cylinders                               |
| <a href="#">P/N: D4H655, Type: 4H-6WB</a>              | Replacement cylinders                               |
| <a href="#">P/N: D4N655, Type: 4N-6WB</a>              | Replacement cylinder                                |
| <a href="#">P/N: D4N355, Type: 4N-3WB</a>              | Replacement cylinders                               |
| <a href="#">LE18D</a>                                  | Built-in steam humidifier with alphanumeric display |
| <a href="#">D3L335</a>                                 | Replacement cylinder                                |
| <a href="#">2560041</a>                                | Steam hose with textile coating                     |
| <a href="#">634-LE05P</a>                              | Configuration card                                  |
| <a href="#">Typ LR50PD mit MT1</a>                     | steam humidifier                                    |
| <a href="#">steam hose with textile cover DN 55</a>    | steam hose with textile jacket, DN 55 mm            |
| <a href="#">C3H335</a>                                 | cylinder                                            |
| <a href="#">CC-2N-2WA</a>                              |                                                     |
| <a href="#">CC-3N-3WA</a>                              | Cylinder for LE18                                   |
| <a href="#">1/2N-2WA</a>                               | Cylinder                                            |
| <a href="#">2N2WA</a>                                  | iSE moisture cylinder                               |
| <a href="#">M990503</a>                                |                                                     |
| <a href="#">3910037</a>                                |                                                     |
| <a href="#">3910166</a>                                |                                                     |
| <a href="#">C3N335</a>                                 |                                                     |
| <a href="#">LR10PD</a>                                 | steam humidifier                                    |
| <a href="#">LR30PD</a>                                 | steam humidifier                                    |
| <a href="#">C4H355</a>                                 |                                                     |
| <a href="#">2560049</a>                                |                                                     |
| <a href="#">C4N355</a>                                 | Replacement cylinder 4N-3WB                         |
| <a href="#">LR30C</a>                                  | maintenance kit                                     |

| Product                                                 | Description                 |
|---------------------------------------------------------|-----------------------------|
| <a href="#">D4NS355</a>                                 | steam humidifier            |
| <a href="#">M990044 (LR60PD, LR30PD, LR50PD)</a>        |                             |
| <a href="#">M990042 (for for JLR50PD)</a>               |                             |
| <a href="#">C2N235</a>                                  |                             |
| <a href="#">D4N655</a>                                  | steam cylinder              |
| <a href="#">1/2N-2WA (D1-2N235)</a>                     | replacement cylinder        |
| <a href="#">3910195</a>                                 | Fill and drain base         |
| <a href="#">LE45D</a>                                   | steam humidifier            |
| <a href="#">PCM2L-3WA</a>                               | spare cylinder 2L-3WA       |
| <a href="#">PCM2N-3WA</a>                               | humidifier                  |
| <a href="#">634-LE30P</a>                               | LE/LEP configuration card   |
| <a href="#">2620320</a>                                 | Inlet valve                 |
| <a href="#">C1-2N235</a>                                |                             |
| <a href="#">2560042</a>                                 | steam hose                  |
| <a href="#">M570001</a>                                 | Electric cap red            |
| <a href="#">D4H655/ 450-1000 uS/cm</a>                  | replacement cylinder        |
| <a href="#">D4N655/ 150-650 uS/cm</a>                   | replacement cylinder        |
| <a href="#">D1N235</a>                                  |                             |
| <a href="#">1097021</a>                                 | heating element             |
| <a href="#">3910173</a>                                 | sealing                     |
| <a href="#">3910246</a>                                 |                             |
| <a href="#">3910109</a>                                 | caseback                    |
| <a href="#">M010234</a>                                 | mounting                    |
| <a href="#">1080150</a>                                 | Safety fuse                 |
| <a href="#">PCM1N-3WA</a>                               | replacement cylinder bank   |
| <a href="#">2N-2WA (D2N35)</a>                          | replacement cylinder        |
| <a href="#">CD1/2HS3WA old code /new code D1-2HS235</a> | steam cylinder              |
| <a href="#">D1-2HS235</a>                               | cylinder                    |
| <a href="#">LE18PD</a>                                  | steam humidifier            |
| <a href="#">D3HS335</a>                                 | Erzatzzylinder              |
| <a href="#">M57-0002</a>                                | White High Water Sensor Cap |
| <a href="#">8040604</a>                                 | electrode cable             |
| <a href="#">1/2L-2WO (D1-2L222)</a>                     | replacement cylinder        |
| <a href="#">2600062</a>                                 | Pump                        |
| <a href="#">LMV4</a>                                    | Minivap                     |
| <a href="#">LE30LC-2</a>                                | steam humidifier            |
| <a href="#">LE45LC-2</a>                                | Other steam humidifier      |
| <a href="#">M9900168</a>                                | Tundish fill cup            |
| <a href="#">40101994</a>                                | PUMP DRAIN                  |
| <a href="#">1097020</a>                                 |                             |
| <a href="#">1/2L-2WA</a>                                | replacement cylinder        |
| <a href="#">3H-3WA</a>                                  | Zylinder                    |
| <a href="#">2560043</a>                                 |                             |
| <a href="#">Type LE05LC</a>                             |                             |
| <a href="#">D2N335</a>                                  | Steam cylinder              |

| Product                                    | Description                          |
|--------------------------------------------|--------------------------------------|
| <a href="#">Type D2N235</a>                | replacement cylinder                 |
| <a href="#">262030</a>                     |                                      |
| <a href="#">V45-VS09D</a>                  |                                      |
| <a href="#">Type D1-2L222</a>              | replacement cylinder                 |
| <a href="#">2560041 DN 35mm</a>            | Steam hose with textile jacket       |
| <a href="#">D4L-6WB</a>                    | replacement cylinder                 |
| <a href="#">2560054</a>                    | Steam Hose                           |
| <a href="#">CONTROL BOARD FOR LE18LC-2</a> |                                      |
| <a href="#">D2N322 / 2N-3WO</a>            | replacement cylinder                 |
| <a href="#">C4NS655</a>                    | evaporator cylinder                  |
| <a href="#">8070004</a>                    | 10m2 cable plug                      |
| <a href="#">4NS-6WB</a>                    | replacement cylinder                 |
| <a href="#">M300120</a>                    |                                      |
| <a href="#">3910112</a>                    | pump cover                           |
| <a href="#">LR40PD</a>                     | steam humidifier                     |
| <a href="#">DH2H235</a>                    | cylinder for steam humidifier LE09LC |
| <a href="#">1/2H-2WA</a>                   |                                      |
| <a href="#">Typ LR20PD</a>                 |                                      |
| <a href="#">Typ LR40PD</a>                 |                                      |
| <a href="#">D3H335/Zylinder 3H-3WA</a>     |                                      |
| <a href="#">3910172</a>                    |                                      |
| <a href="#">FVKIT 118</a>                  |                                      |
| <a href="#">1110401</a>                    |                                      |
| <a href="#">1210080</a>                    |                                      |
| <a href="#">VE18-3P</a>                    |                                      |
| <a href="#">VE45-3P</a>                    | steam humidifier                     |
| <a href="#">D4L655</a>                     | Replacement cylinder                 |
| <a href="#">M540180</a>                    |                                      |
| <a href="#">D4N355 / 150-650 pS/cm</a>     |                                      |